

Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240VAC, Terminal Screws

By Hubbell Wiring Device-Kellems
Catalog # CPB21



Switches and Lighting Controls, Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240VAC, Terminal Screws, Yellow, with Interlock.

Performance

Environmental - Operating Temperatures - Max Continuous- 75 ° C, Minimum -40° w/o Impact

General

Actuator	Push Buttons
Catalog Number	CPB21
Contact Configuration	Momentary
EU RoHS Indicator	No
Enclosure Type	NEMA 4X
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	None
Ingress Protection	IP55
Material - Mounting Hardware	Cable Mounted
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Compact
Style	Two Button
Type	Single Speed
UPC	783585106854

Dimensions

Dimensions	9.13 in x 1.06 in x 2.38 in
Display Size	Compact
Height	2.38 in

Length	9.13 in
Weight	0.75 lb
Width	1.06 in

Electrical Ratings

Amperage Rating	120V AC- 6A, 240V AC 35% PF- 3A, 125V DC- 1.1A, Inductive 250V- .55 A
Connectivity	Terminal Screws
Contact Rating	Pilot Duty Only
Phase	Single Phase

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA 4X

Logistics

Carton Quantity	25
Pallet Quantity	1500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - CPB21](#)
[Warranty - Industrial & Commercial Products](#)