

**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices,  
Receptacles, Duplex, Commercial  
Grade, 2-Pole 3-Wire Grounding,  
15A 125V, 5-15R, Light Almond,  
Single Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [CR15LA](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade,  
2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Light Almond, Single  
Pack.



## General

Application	Commercial Specification Grade
Catalog Number	CR15LA
Color	Light Almond
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - UL 94 V-2  Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)  Mechanical - Product Identification - Ratings are a permanent part of the device  Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only  Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Commercial Specification Grade
Style	Smooth Face
Type	Standard Duplex  Standard Duplex
UPC	783585127583

## Dimensions

Dimensions	1.32 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.15 lb
Width	0.83 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA, C22.2, No. 42  Fed. Spec. W-C-596  NEMA® WD-6 Compliant  UL Listed to UL498 File No. E2186
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	9000

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-CR15LA-SPEC-EN | REV 6/2024