

## Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [CR20GRY](#)



Straight Blade Devices, Receptacles, Duplex, Commercial Grade,  
2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack.

### Application

- Commercial Specification Grade

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	CR20GRY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none"> <li>Automatic Self-grounding Staple - Stainless steel</li> <li>Base - Nylon</li> <li>Face - Nylon</li> <li>Mounting Screws - Galvanized steel</li> <li>Mounting Strap - .040 in. (1) Galvanized steel</li> </ul>

Style  
Type  
UPC

- Power Contacts - .030 in. (.8) Brass
  - Terminal Screws - Plated steel
- Smooth Face  
Standard Duplex  
783585900124

### Dimensions

Dimensions	1.32 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.2 lb
Width	0.83 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>Certified to CSA, C22.2, No. 42</li> <li>Fed. Spec. W-C-596</li> <li>NEMA® WD-6 Compliant</li> <li>UL Listed to UL498 File No. E2186</li> </ul>
Nema Rating	5-20R

Standards - RoHS Compliance CM  
Status

### Logistics

Carton Quantity 10  
Pallet Quantity 9000

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CR20GRY](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-CR20GRY-SPEC-EN | REV 10/2024