

**HUBBELL**  
Wiring Device-Kellems

**Specification Grade Commercial  
Series, Toggle Switches, General  
Purpose AC, Single Pole, 20A  
120/277V AC, Side Wired Only  
Toggle**

By Hubbell Wiring Device-Kellems  
Catalog # [CS120I](#)

Switches and Lighting Controls, Specification Grade Commercial  
Series, Toggle Switches, General Purpose AC, Single Pole, 20A  
120/277V AC, Side Wired Only, Ivory Toggle.



## Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 20A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

## General

Catalog Number	CS120I
Color	Ivory
EU RoHS Indicator	Yes
Item Type	Single Pole Toggle Switch
Material	Nylon
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	General Purpose
Specifications	<ul style="list-style-type: none"><li>Auto Grounding Mounting Bridge - Zinc Plated Steel</li><li>Base Material - Thermoplastic, Black</li><li>Contacts - Silver Alloy</li><li>Ground Screw - Brass (Green)</li><li>Terminal Screws - Brass</li><li>Toggle Material - Nylon</li><li>Top Material - Thermoplastic, Gray</li></ul>
Style	Single Pole

Type  
UPC

Toggle  
783585901152

## Dimensions

Dimensions	4.18 in x 1.49 in x 1.83 in
Height	1.83 in
Length	4.18 in
Weight	0.15 lb
Width	1.49 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	4050

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CS120I](#)  
[Warranty - Industrial & Commercial Products](#)

