

## Switches and Lighting Controls, Toggle Switch, Commercial Grade, Three Way, 15A 120/277V AC, Side Wired, Brown Toggle

By Hubbell Wiring Device-Kellems  
Catalog # [CS315](#)



Switches and Lighting Controls, Toggle Switch, Commercial Grade, Three Way, 15A 120/277V AC, Side Wired, Brown Toggle.

### Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

### General

Action	SPDT
Catalog Number	CS315
Color	Brown
EU RoHS Indicator	Yes
Item Type	Three Way Toggle Switch
Material	Nylon
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	General Purpose
Specifications	<ul style="list-style-type: none"><li>• Auto Grounding Mounting Bridge - Zinc Plated Steel</li><li>• Base Material - Thermoplastic, Black</li><li>• Contacts - Silver Alloy</li><li>• Ground Screw - Brass (Green)</li><li>• Terminal Screws - Brass</li><li>• Toggle Material - Nylon</li><li>• Top Material - Thermoplastic, Gray</li></ul>
Style	Three Way

Type	Toggle
UPC	783585902005

### Dimensions

Dimensions	4.18 in x 1.49 in x 1.83 in
Height	1.83 in
Length	4.18 in
Weight	0.15 lb
Width	1.49 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

### Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

### Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Pallet Quantity	4050

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CS315](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand