

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel

By Hubbell Wiring Device-Kellems
Catalog # [CS6375](#)



Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

General

Catalog Number	CS6375
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single Flanged Inlet
Material	Steel, Zinc Plated
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Blades - Brass• Casing - Steel, zinc plated• Terminal Retainer - Phenolic• Terminal Screws - Steel
Type	Flanged Inlet
UPC	783585828206

Dimensions

Dimensions	2.17 in x 3.50 in x 2.62 in
Display Size	Standard Sized Product

Height	2.62 in
Length	2.17 in
Weight	0.85 lb
Width	3.5 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Listed to UL 498
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	810

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - CS6375](#)
[Warranty - Industrial & Commercial Products](#)