

# Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 50A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems  
Catalog # [CS8264C](#)

Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 50A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG stranded copper wire only

## General

Catalog Number	CS8264C
Color	Black, White
Cord Range	.830"-1.250"(21.08-31.75)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Insulgrip Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Contacts - Brass</li><li>• Cord Grip - Polyester</li><li>• Housing - Nylon</li><li>• Terminal Retainer - Thermoplastic polyester</li><li>• Terminal Screws - Stainless Steel</li></ul>
Type	Connector Body
UPC	783585828466

## Dimensions

Dimensions 6.50 in x 2.56 in x 2.50 in

Display Size	Standard
Height	2.5 in
Length	6.5 in
Weight	0.95 lb
Width	2.56 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Cable Range	0.830 - 1.250 in
Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Listed to UL 498</li></ul>
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	1
Pallet Quantity	1190

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CS8264C](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-CS8264C-SPEC-EN | REV 10/2024