

Straight Blade Devices, Receptacle, Tamper Resistant Decorator Duplex, Commercial Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, With Night Light

By Hubbell Wiring Device-Kellems
Catalog # [DR15NLWH](#)



Straight Blade Devices, Receptacle, Tamper Resistant Decorator Duplex, Commercial Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, With Night Light, White.

Performance

- Electrical - Color Temperature - 3400K - 3600K
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Electrical - LED Energy Consumed - 0.5 watt
- Electrical - Light Output - 0.5 Lumens
- Electrical - Rating - 15A, 125VAC Only
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

| | |
|------------------------------|---|
| Catalog Number | DR15NLWH |
| EU RoHS Indicator | Contact Manufacturer |
| Horsepower - Maximum | 0.5 |
| Item Type | Decorator Duplex |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Specifications | <ul style="list-style-type: none"> • Automatic Self-grounding Staple - Stainless steel • Base - Nylon • Face - Nylon • Lens - Polycarbonate • Mounting Screws - Zinc Plated Steel • Mounting Strap - Galvanized Steel • Power Contacts - .030 in. (.8) Brass • Terminal Screws - Plated Steel |

UPC

- Wire Clamp - .062 in. (1.6) Nickel plated steel
783585541341

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.29 in x 1.15 in x 1.29 in |
| Display Size | Standard Sized Product |
| Height | 1.29 in |
| Length | 3.29 in |
| Width | 1.15 in |

Electrical Ratings

| | |
|---------------------------|---------------------------|
| Amperage Rating | 15 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Voltage Rating | 125 VAC |
| Wattage | 1875 W |

Conductor Related

| | |
|-----------------|------------------|
| Number Of Wires | 3-Wire Grounding |
|-----------------|------------------|

Certifications And Compliance

| | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186 |
| Nema Rating | 5-15R |

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 4500 |

Product Assets

