

Straight Blade Devices, Receptacles, Duplex, Decorator, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [DR20GRY](#)



Straight Blade Devices, Receptacles, Duplex, Decorator,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5-20R, Gray, Single Pack.

Application

- Commercial Specification Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	DR20GRY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - Nylon• Face - Nylon• Ground Contacts - Brass

- Mounting Screws - Galvanized Steel
- Mounting Strap - .040 in. (1) Galvanized steel
- Power Contacts - .030 in. (.8) Brass
- Terminal Screws - Plated steel
- Wire Clamp - .062 in. (1.6) Nickel plated steel

Style
Type
UPC

Style Line Decorator
Standard Duplex
783585127897

Dimensions

Dimensions	3.28 in x 1.06 in x 1.29 in
Display Size	Standard Sized Product
Height	1.29 in
Length	3.28 in
Weight	0.2 lb
Width	1.06 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)

- Certified to CSA, C22.2, No. 42
 - Fed. Spec. W-C-596
 - NEMA® WD-6 Compliant
 - UL Listed to UL498 File No. E2186
- 5-20R

Nema Rating

Carton Quantity

10

Pallet Quantity

9000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - DR20GRY](#)

[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-DR20GRY-SPEC-EN | REV 10/2024