

# Straight Blade Devices, Receptacles, Tamper-Resistant Duplex, Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R



By Hubbell Wiring Device-Kellems  
Catalog # [DR20WHITR](#)

Straight Blade Devices, Receptacles, Tamper-Resistant Duplex,  
Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire  
Grounding, 20A 125V, 5-20R, White, Single Pack.

## Application

- Commercial Specification Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	DR20WHITR
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none"><li>• Automatic Self-grounding Staple - Stainless steel</li><li>• Base - Nylon</li><li>• Face - Nylon</li></ul>

- Mounting Screws - Galvanized steel
  - Mounting Strap - .040 in. Galvanized steel
  - Power Contacts - .030 in. (.8) Brass
  - Terminal Screws - Plated steel
  - Wire Clamp - .062 in. (1.6) Nickel plated steel
- Style Line Decorator  
Tamper-Resistant  
783585144443

Style  
Type  
UPC

## Dimensions

Dimensions	3.28 in x 1.14 in x 1.29 in
Display Size	Standard Sized Product
Height	1.29 in
Length	3.28 in
Weight	0.15 lb
Width	1.14 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	8000

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Specifications - DR20WHITR](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-DR20WHITR-SPEC-EN | REV 10/2024