

DIN Rail Utility Box, Complete Unit-Duplex Receptacle, 1) 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

By Hubbell Wiring Device-Kellems
Catalog # [DRUB15](#)



DIN Rail Utility Box, Complete Unit- Duplex Receptacle, 1) 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray.

General

Catalog Number	DRUB15
Color	Gray
Construction	Molded and Fabricated
EU RoHS Indicator	Yes
Horsepower - Maximum	0.5
Item Type	Complete Unit
Knockouts	None
Material - Mounting Hardware	Vertical Mount, DIN Rail Mount
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none">• Base - PVC• Cover/Faceplate - PVC• Plug - PVC
Type	Box and Device
UPC	783585108001

Dimensions

Dimensions	5.62 in x 3.31 in x 2.54 in
Display Size	Standard Sized Product
Height	2.54 in
Length	5.62 in
Weight	1 lb
Width	3.31 in

Electrical Ratings

Amperage Rating	15 A
-----------------	------

Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Entry	Terminals
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, Certified to CSA
Nema Rating	5-15R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	5
Pallet Quantity	560

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - DRUB15](#)
[Warranty - Industrial & Commercial Products](#)