

Complete Unit- IG, DIN Rail Box, 15A, IG, Gray

By Hubbell Wiring Device-Kellems
Catalog # [DRUBIG15](#)



Complete Unit- IG, DIN Rail Box, 15A, IG, Gray.

General

Catalog Number	DRUBIG15
Color	Gray
Construction	Molded and Fabricated
EU RoHS Indicator	No
Horsepower - Maximum	0.5
Item Type	Complete Unit
Knockouts	None
Material - Mounting Hardware	Vertical Mount, DIN Rail Mount
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none">• Base - PVC• Cover/Faceplate - PVC• Plug - PVC
Type	Box and Device
UPC	783585108100

Dimensions

Dimensions	5.62 in x 3.31 in x 2.54 in
Display Size	Standard Sized Product
Height	2.54 in
Length	5.62 in
Weight	1.05 lb
Width	3.31 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Entry	Terminals
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - DRUBIG15](#)
- [Warranty - Industrial & Commercial Products](#)