

## DIN Rail Utility Box, Complete Unit- TVSS, DIN Rail Box, 15A TVSS, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [DRUBTVSS15](#)



DIN Rail Utility Box, Complete Unit- TVSS, DIN Rail Box, 15A  
TVSS, Gray.

### General

Catalog Number	DRUBTVSS15
Color	Gray
Construction	Molded and Fabricated
EU RoHS Indicator	No
Horsepower - Maximum	0.5
Item Type	Complete Unit
Knockouts	None
Material - Mounting Hardware	Vertical Mount, DIN Rail Mount
Number Of Poles	2-Pole
Type	Box and Device
UPC	783585108117

### Dimensions

Dimensions	5.62 in x 3.31 in x 2.54 in
Display Size	Standard Sized Product
Height	2.54 in
Length	5.62 in
Weight	1.1 lb
Width	3.31 in

### Electrical Ratings

Amperage Rating	15 A
-----------------	------

Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Cable Entry	Terminals
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - DRUBTVSS15](#)  
[Warranty - Industrial & Commercial Products](#)