

# Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 3/8", 100 feet

By Hubbell Wiring Device-Kellems  
Catalog # [G1038](#)



Kellems Wire Management, Liquidtight System, Non-Metallic  
PolyTuff® I Conduit, Gray, 3/8", 100 feet

## General

Application	UL1660
Catalog Number	G1038
Color	Gray
EU RoHS Indicator	Yes
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	Electrical - Voltage Rating - 600V Maximum  Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)  Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)  Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)
Type	PolyTuff® I Liquidtight Conduit  PolyTuff® I Liquidtight Conduit
UPC	783585497983

## Dimensions

Length	100 ft
Trade Size	3/8
Width	0.7 in

## Electrical Ratings

Voltage Rating	600 V
----------------	-------

## Certifications And Compliance

Industry Standard(s)	Meets Requirements Of NEC  UL Listed 1660. Approved For Outdoor And Direct Burial
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	100
Pallet Quantity	2000

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-G1038-SPEC-EN | REV 6/2024