



Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 3/4", 100 feet

By Hubbell Wiring Device-Kellems
Catalog # [G1075](#)



Kellems Wire Management, Liquidtight System, Non-Metallic
PolyTuff® I Conduit, Gray, 3/4", 100 feet

Application

UL1660

General

Color	<ul style="list-style-type: none">GrayGris
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none">Electrical - Voltage Rating - 600V MaximumEnvironmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)
Type	<ul style="list-style-type: none">PolyTuff® I Liquidtight ConduitPolyTuff® I Liquidtight Conduit
UPC	783585498003

Dimensions

Length	100 ft
Trade Size	3/4
Width	1.04 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">Meets Requirements Of NECUL Listed 1660. Approved For Outdoor And Direct Burial
----------------------	------------------------------------------------------------------------------------------------------------------------------------------

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	100
Pallet Quantity	2000

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Wire Management Solutions Brochure](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-G1075-SPEC-EN | REV 1/2024