



Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1", 100 feet

By Hubbell Wiring Device-Kellems
Catalog # [G1100](#)



Kellems Wire Management, Liquidtight System, Non-Metallic
PolyTuff® I Conduit, Gray, 1", 100 feet

Application

UL1660

General

| | |
|---------------|--|
| Color | <ul style="list-style-type: none">• Gray• Gris |
| Finish Type | Smooth |
| Item Type | Standard Product |
| Load Capacity | Extra Flexible |
| Material | Co-extruded rigid and flexible PVC |
| Performance | <ul style="list-style-type: none">• Electrical - Voltage Rating - 600V Maximum• Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)• Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)• Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C) |
| Type | <ul style="list-style-type: none">• PolyTuff® I Liquidtight Conduit• PolyTuff® I Liquidtight Conduit |
| UPC | 783585333656 |

Dimensions

| | |
|------------|---------|
| Length | 100 ft |
| Trade Size | 1 |
| Width | 1.30 in |

Electrical Ratings

| | |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Certifications and Compliance

| | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">• Meets Requirements Of NEC• UL Listed 1660. Approved For Outdoor And Direct Burial |
|----------------------|--|

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------|------|
| Carton Quantity | 100 |
| Pallet Quantity | 2000 |

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Wire Management Solutions Brochure](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-G1100-SPEC-EN | REV 1/2024