



# Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1-1/4", 100 feet

By Hubbell Wiring Device-Kellems  
Catalog # [G1125](#)



Kellems Wire Management, Liquidtight System, Non-Metallic  
PolyTuff® I Conduit, Gray, 1-1/4", 100 feet

## Application

UL1660

## General

Color	<ul style="list-style-type: none"><li>• Gray</li><li>• Gris</li></ul>
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none"><li>• Electrical - Voltage Rating - 600V Maximum</li><li>• Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)</li><li>• Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)</li><li>• Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)</li></ul>
Type	<ul style="list-style-type: none"><li>• PolyTuff® I Liquidtight Conduit</li><li>• PolyTuff® I Liquidtight Conduit</li></ul>
UPC	783585333663

## Dimensions

Length	100 ft
Trade Size	1 1/4
Width	1.65 in

## Electrical Ratings

Voltage Rating	600 V
----------------	-------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Meets Requirements Of NEC</li><li>• UL Listed 1660. Approved For Outdoor And Direct Burial</li></ul>
----------------------	--

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Carton Quantity	100
Pallet Quantity	600

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-G1125-SPEC-EN | REV 1/2024