



Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 2", 50 feet

By Hubbell Wiring Device-Kellems
Catalog # [G1200](#)



Kellems Wire Management, Liquidtight System, Non-Metallic
PolyTuff® I Conduit, Gray, 2", 50 feet

Features

- No jagged metal edges
- Rigid PVC core bonded to flexible PVC jacket
- Non-metallic construction ends metal fatigue and separation problems

Application

UL1660

General

Color	<ul style="list-style-type: none">• Gray• Gris
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none">• Electrical - Voltage Rating - 600V Maximum• Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)• Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)• Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)
Type	<ul style="list-style-type: none">• PolyTuff® I Liquidtight Conduit• PolyTuff® I Liquidtight Conduit
UPC	783585333687

Dimensions

Length	50 ft
Trade Size	2
Width	2.36 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Meets Requirements Of NEC• UL Listed 1660. Approved For Outdoor And Direct Burial
----------------------	--

Logistics

Carton Quantity	50
Pallet Quantity	350

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Wire Management Solutions Brochure](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-G1200-SPEC-EN | REV 1/2024

