

HUBBELL
Wiring Device-Kellems

GFP15M

By Hubbell Wiring Device-Kellems
Catalog # [GFP15M](#)

Power Protection Products, GFCI Portables, Commercial, Manual Set, 15A 120V AC, 5-15R, 6' Cord Length, 4-6 mA Trip Level, Yellow



General

Application	Multiple Outlet Portable GFCI
Catalog Number	GFP15M
Color	Yellow
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Thermoplastic
Material - Mounting Hardware	Multi-Outlet Box
Number Of Poles	2-Pole
Series	Extra Heavy Duty
Style	Manual Set
Type	Multiple Outlet
UPC	783585521053

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	1
Pallet Quantity	154

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Portable GFCI Devices](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-GFP15M-SPEC-EN | REV 6/2024