

GFP20M

By Hubbell Wiring Device-Kellems
Catalog # [GFP20M](#)

Power Protection Products, GFCI Portables, Commercial, Manual Set, 20A 120V AC, 5-20R, 6' Cord Length, 4-6 mA Trip Level, Yellow



Application

Multiple Outlet Portable GFCI

General

Catalog Number	GFP20M
Color	Yellow
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Thermoplastic
Material - Mounting Hardware	Multi-Outlet Box
Number Of Poles	2-Pole
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">Cover - PBTFlap - PBTHousing - PBTScrews - Zinc plated steel
Style	Manual Set
Type	Multiple Outlet
UPC	783585521107

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	2500

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Portable GFCI Devices](#)
[Specifications - GFP20M](#)
[Warranty - Industrial & Commercial Products](#)