



GFTWRST82W

By Hubbell Wiring Device-Kellems
Catalog # [GFTWRST82W](#)

Straight Blade Devices, Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Color	<ul style="list-style-type: none">• White• Blanc
EU RoHS Indicator	Contact Manufacturer
Series	Hospital Grade
Style	Standard
Type	<ul style="list-style-type: none">• Tamper-Resistant, Weather Resistant• Tamper-Resistant, Weather Resistant
UPC	783585485331

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-GFTWRST82W-SPEC-EN | REV 1/2024