

Straight Blade Devices, IEC 320 Devices, Female Receptacle, 16A 250V, International Rated, Pressure Screw Terminal, Black, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [H320R](#)



Straight Blade Devices, IEC 320 Devices, Female Receptacle, 16A 250V, International Rated, Pressure Screw Terminal, Black, Single Pack.

Application

- Heavy Duty

Performance

- Electrical: Dielectric Voltage Withstands 2,000V minimum, Rating 16A 250V AC for European service
- 20A 250V AC for ,North American service
- Mechanical: Terminal Accommodation North American - #16-12 AWG stranded or solid copper conductor only. International - 1.55mm²-2.5mm², Terminal Identification: Terminals identified in accordance with UL 498 and CSA
- Environmental: Flammability UL 94 VO , Operating Temperatures Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	H320R
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	IEC Appliance Coupler Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Zinc plated steel• Device Type - 2 Pole + earth• Housing - Nylon• Power Contacts - .032" (.81) Brass• Terminal Clamp - Nickel plated steel• Terminal Retainer - Nylon• Terminal Screws - Stainless steel
UPC	783585777054

Dimensions

Dimensions	1.41 in x 1.89 in x 1.52 in
Display Size	Standard Sized Product
Height	1.52 in
Length	1.41 in
Weight	0.1 lb
Width	1.89 in

Electrical Ratings

Amperage Rating	20/16 A
Connectivity	Screw Terminals
Current / Amperage Rating	20/16 A
Current Rating	20/16 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	7500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	North American-#16AWG-#12AWG; International-1.55mm ² -2.5mm ² .

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA certified 20A 250V AC-File No. 17337• UL Listed 20A 250V AC-File No. E2186
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	2640



A Hubbell brand