

Commercial Grade, Panel Mount and Specialty Switches, Bat Handle Switches, Single Pole Single Throw, 10A 250V/10A 125V, Terminal Screws,

By Hubbell Wiring Device-Kellems
Catalog # [HBL11](#)



Switches and Lighting Controls, Commercial Grade, Panel Mount and Specialty Switches, Bat Handle Switches, Single Pole Single Throw, 10A 250V/10A 125V, Terminal Screws,

Performance

Environmental - Operating Temperatures - Max Continuous- 75 °C, Minimum -40 °C Without Impact

General

Action	SPST
Catalog Number	HBL11
Color	Metallic
EU RoHS Indicator	No
Horsepower - Maximum	0.75
Item Type	Panel Mount and Bat Handle Switch
Mounting Method	Panel Mount
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Single Pole/Single Throw
Specifications	<ul style="list-style-type: none">• Body Material - Impact Resistant Thermoplastic Body• Bushing - Brass- Nickel Plated• Contacts - Fine Silver• Strap Material - Nickel Plated• Toggle - Brass- Nickel Plated
Style	Screw Terminal

Type	General Purpose
UPC	783585016672

Dimensions

Dimensions	2.2 in x 0.56 in x 1.13 in
Height	1.13 in
Length	2.2 in
Weight	0.05 lb
Width	0.56 in

Electrical Ratings

Amperage Rating	10/20 A
Connectivity	Screw Terminals
Current / Amperage Rating	10/20 A
Voltage Rating	250/125 VAC

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL11](#)
[Warranty - Industrial & Commercial Products](#)