



# Industrial Grade, Pilot Light Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired Toggle

By Hubbell Wiring Device-Kellems  
Catalog # [HBL1221PL](#)



Switches and Lighting Controls, Industrial Grade, Pilot Light Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired, Red Toggle

## Features

- Large brass binding head screws with deep slots
- Abuse resistant nylon toggle
- Strip gauge for accurate wiring

## Application

Back and Side Wired

## General

Color	<ul style="list-style-type: none"> <li>• Red</li> <li>• Rouge</li> </ul>
Indicator	Light On with Load On
Item Type	Single Pole Pilot Light Switch
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute</li> <li>• Electrical - Max. Continuous Current - 20A</li> <li>• Electrical - Max. Working Voltage - 277V AC</li> <li>• Electrical - Overload - Minimum 4.8 times rated current for 100 cycles</li> <li>• Electrical - Temperature Rise - 30°C maximum at rated current</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact</li> <li>• Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. Solid and stranded copper wire only</li> </ul>

## Dimensions

Dimensions	4.06 in x 1.31 in x 1.86 in
Height	1.86 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Literature - Healthcare Product Solutions](#)  
[Warranty - Industrial & Commercial Products](#)

Series	Extra Heavy Duty
Style	Single Pole
Type	<ul style="list-style-type: none"><li>• Toggle</li><li>• Toggle</li></ul>
UPC	783585431468

---



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL1221PL-SPEC-EN | REV 1/2024