

# Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnect Accessories, NEMA 1 Enclosure Only, 40A 600V AC

By Hubbell Wiring Device-Kellems  
Catalog # [HBL1370](#)



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Motor Disconnect Accessories, NEMA 1 Enclosure Only,  
40A 600V AC

## Application

- For 30A Switches

## Performance

Environmental - Operating Temperatures - Max Continuous- 75  
°C, Minimum- -40 °C w/o Impact

## General

Catalog Number	HBL1370
EU RoHS Indicator	No
Enclosure Type	NEMA 1
Environmental Conditions	Indoor Only
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused
Specifications	<ul style="list-style-type: none"><li>• Base Material - Steel</li><li>• Cover Material - Thermoplastic</li><li>• No. Equipment Grounds - 1</li></ul>
Style	Standard Duty
Type	Enclosures without Switch
UPC	783585016986

## Dimensions

Dimensions	4.52 in x 3.2 in x 3.15 in
Height	3.15 in
Length	4.52 in
Weight	0.6 lb
Width	3.2 in

## Electrical Ratings

Amperage Rating	30 A
Current Rating	30 A

## Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	960

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL1370](#)  
[Warranty - Industrial & Commercial Products](#)