

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnect Accessories, NEMA 1 Enclosure Only, 40A 600V AC

By Hubbell Wiring Device-Kellems
Catalog # [HBL1370](#)

Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Motor Disconnect Accessories, NEMA 1 Enclosure Only,
40A 600V AC

Application

- For 30A Switches

Performance

Environmental - Operating Temperatures - Max Continuous- 75
°C, Minimum- -40 °C w/o Impact

General

Catalog Number	HBL1370
EU RoHS Indicator	No
Enclosure Type	NEMA 1
Environmental Conditions	Indoor Only
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused
Specifications	<ul style="list-style-type: none">• Base Material - Steel• Cover Material - Thermoplastic• No. Equipment Grounds - 1
Style	Standard Duty
Type	Enclosures without Switch
UPC	783585016986

Dimensions



Dimensions	4.52 in x 3.2 in x 3.15 in
Height	3.15 in
Length	4.52 in
Weight	0.6 lb
Width	3.2 in

Electrical Ratings

Amperage Rating	30 A
Current Rating	30 A

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	960

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL1370](#)
[Warranty - Industrial & Commercial Products](#)