

**HUBBELL**  
Wiring Device-Kellems

**Extra Heavy Duty Industrial Grade,  
Toggle Switches, General Purpose  
AC, Double Pole Double Throw  
Center Off, 30A 120/277V AC  
Toggle**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL1388](#)

Switches and Lighting Controls, Extra Heavy Duty Industrial  
Grade, Toggle Switches, General Purpose AC, Double Pole  
Double Throw Center Off, 30A 120/277V AC, Back and Side  
Wired, Brown Toggle



## Application

Back and Side Wired

## Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 30A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. Solid and stranded copper wire only

## General

Action	DPDT
Catalog Number	HBL1388
Color	Brown
EU RoHS Indicator	No
Number Of Poles	Double Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>Base Material - Thermoset, Green</li><li>Contacts - Silver Alloy</li><li>Ground Screw - Brass (Green)</li><li>Terminal Screws - Brass</li><li>Toggle Material - Nylon</li><li>Top Material - Thermoset</li></ul>
Style	Double Pole Double Throw

Type  
UPC

Toggle  
783585432700

## Dimensions

Dimensions	4.06 in x 1.31 in x 1.89 in
Height	1.89 in
Length	4.06 in
Weight	0.25 lb
Width	1.31 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
Pallet Quantity	4500

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL1388](#)  
[Warranty - Industrial & Commercial Products](#)

