

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Non-Metallic NEMA 1 Enclosure, For 30A Devices, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL1390](#)



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Motor Disconnects, Non-Metallic NEMA 1 Enclosure,
For 30A Devices , Black

Application

- For 30A Switches

Performance

Environmental - Operating Temperatures - Max Continuous- 75
°C, Minimum- -40 °C w/o Impact

General

Catalog Number	HBL1390
EU RoHS Indicator	No
Enclosure Type	NEMA 1
Environmental Conditions	Indoor Only
Horsepower - Maximum	20
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused
Specifications	<ul style="list-style-type: none">• Base Material - Aluminum• Cover Material - Aluminum• No. Equipment Grounds - 2
Style	Standard Duty
Type	Enclosures without Switch
UPC	783585017020

Dimensions

Dimensions	4.52 in x 3.97 in x 3.43 in
Height	3.43 in
Length	4.52 in
Weight	1.05 lb
Width	3.97 in

Electrical Ratings

Amperage Rating	30 A
Current Rating	30 A

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	810

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL1390](#)
[Warranty - Industrial & Commercial Products](#)