

Straight Blade Devices, Male Plug, Elasto-Grip Dust Tight, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 125V, 5-20P

By Hubbell Wiring Device-Kellems
Catalog # [HBL1433](#)



Straight Blade Devices, Male Plug, Elasto-Grip Dust Tight,
Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding,
20A 125V, 5-20P, Yellow, Single Pack.

Application

Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL1433
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Elastogrip
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Elastogrip
Specifications	<ul style="list-style-type: none">• Assembly Screws - Plated steel• Blade Holder - Nylon• Blades - .060" (1.5) Brass• Housing - PVC• Terminal Clamp - Nickel plated steel• Terminal Retainer - Clear Polycarbonate

Style	Standard
Type	Plug
UPC	783585013336
	<ul style="list-style-type: none">• Terminal Screws - #8-32 Brass , multiple drive

Dimensions

Dimensions	2.19 in x 2.19 in x 1.55 in
Display Size	Standard Sized Product
Height	1.55 in
Length	2.19 in
Weight	0.15 lb
Width	2.19 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified to C22.2 No. 42 File 280• NEMA® WD-6 Compliant• UL Listed to UL498 File E1706
Nema Rating	5-20P

Logistics

Carton Quantity

10

Catalogs - WDK Catalog Full 2024

Specifications - HBL1433

Warranty - Industrial & Commercial Products

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL1433-SPEC-EN | REV 10/2024