

Straight Blade Devices, Male Plug, Elasto-Grip Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P



By Hubbell Wiring Device-Kellems
Catalog # [HBL14W33](#)

Straight Blade Male Plug, Elasto-Grip Watertight,
Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding,
20A 125V, 5-20P

Application

- Industrial/Commercial Grade

Performance

- Electrical:Current Interrupting Certified for current interrupting at full rated current,Dielectric Voltage Withstands 2,000V minimum
- MechanicalProduct Identification Ratings are a permanent part of the device
- Terminal Accommodation #18-#12 AWG. Stranded copper wire only.
- Terminal Identification:Terminals identified in accordance with UL 498 and CSA
- Environmental:Flammability UL 94 V-2,IP Suitability IP55,Operating Temperatures: Maximum continuous 75°C minimum -40°C (w/o impact)

General

Catalog Number	HBL14W33
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Elastogrip
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Elastogrip
Specifications	<ul style="list-style-type: none">Assembly Screws - Plated steelBlade Holder - NylonBlades - .060" (1.5) BrassHousing - PVCTerminal Clamp - Nickel plated steelTerminal Retainer - Clear Polycarbonate

Style
Type
UPC

- Terminal Screws - #8-32 Brass , multiple drive
- Standard
Plug
783585013329

Dimensions

Dimensions	2.67 in x 1.55 in x 2.67 in
Display Size	Standard Sized Product
Height	2.67 in
Length	2.67 in
Weight	0.3 lb
Width	1.55 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">CSA Certified to C22.2 No. 42 File 280NEMA® WD-6 CompliantUL Listed to UL498 File E1706
Nema Rating	5-20P

Logistics

Carton Quantity 10
Pallet Quantity 4050

Catalogs - WDK Catalog Full 2024
Specifications - HBL14W33
Warranty - Industrial & Commercial Products

Product Assets



©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL14W33-SPEC-EN | REV 10/2024