

HUBBELL
Wiring Device-Kellems

**Industrial Grade, Toggle Switches,
General Purpose AC, Momentary
Single Pole Double Throw Center
Off, 15A 120/277V AC, Terminal
Screws, Brown Toggle**

By Hubbell Wiring Device-Kellems
Catalog # [HBL1556](#)

Switches and Lighting Controls, Industrial Grade, Toggle
Switches, General Purpose AC, Momentary Single Pole Double
Throw Center Off, 15A 120/277V AC, Terminal Screws, Brown
Toggle



Application

- Back and Side Wired

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. Solid and stranded copper wire only

General

Action	SPDT
Catalog Number	HBL1556
Color	Brown
Contact Configuration	Momentary
EU RoHS Indicator	No
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Base Material - Thermoset, Blue• Contacts - Silver Alloy• Ground Screw - Brass (Green)• Terminal Screws - Brass• Toggle Material - Nylon• Top Material - Thermoset
Style	Single Pole Double Throw

Type
UPC

Toggle
783585432748

Dimensions

Dimensions	4.06 in x 1.31 in x 1.89 in
Height	1.89 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL1556](#)
[Warranty - Industrial & Commercial Products](#)