

HUBBELL
Wiring Device-Kellems

**Industrial Grade, Toggle Switches,
General Purpose AC, Momentary
Single Pole Double Throw Center
Off, 20A 120/277V AC, Terminal
Screws Toggle**

By Hubbell Wiring Device-Kellems
Catalog # [HBL1557W](#)

Switches and Lighting Controls, Industrial Grade, Toggle
Switches, General Purpose AC, Momentary Single Pole Double
Throw Center Off, 20A 120/277V AC, Terminal Screws, White
Toggle



Application

Back and Side Wired

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 20A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. Solid and stranded copper wire only

General

Action	SPDT
Catalog Number	HBL1557W
Color	White
Contact Configuration	Momentary
EU RoHS Indicator	No
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">Base Material - Thermoset, RedContacts - Silver AlloyGround Screw - Brass (Green)Terminal Screws - BrassToggle Material - NylonTop Material - Thermoset
Style	Single Pole Double Throw

Type
UPC

Toggle
783585432908

Dimensions

Dimensions	4.06 in x 1.31 in x 1.89 in
Height	1.89 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	4050

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL1557W](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL1557W-SPEC-EN | REV 10/2024