

## Single Pole Products, Female Plug, 150 Amp Series, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL15FBK](#)



Single Pole Products, Female Plug, 150 Amp Series, Black

### Application

- Temporary Electrical Power

### Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

### General

Catalog Number	HBL15FBK
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Female Plug
Material	Brass and Non-Metallic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none"><li>• Base Compound - Thermoplastic Elastomer (TPE)</li><li>• Contact Material - Brass</li><li>• Retaining Screw Material - Nylon</li></ul>
Style	Female
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	783585458373

### Dimensions

Display Size	Standard
--------------	----------

### Electrical Ratings

Amperage Rating	150 A
Connectivity	Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Voltage Rating Description	600V AC/DC

### Conductor Related

Conductor Range	#8 AWG to #2 AWG SC/PPC Wire
Number of Conductors	1 Conductor

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• National Electric Code (NEC), ANSI/NFPA 70</li><li>• UL and cUL Listed</li><li>• UL Enclosure Types 3R, 4X, 12</li></ul>
Nema Rating	Non-NEMA

### Logistics

Carton Quantity	25
Pallet Quantity	4500

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Single Pole Devices](#)  
[Specifications - HBL15FBK](#)  
[Warranty - Industrial & Commercial Products](#)