

Single Pole Products, Female Plug, 150 Amp Series, Green

By Hubbell Wiring Device-Kellems
Catalog # [HBL15FGN](#)



Single Pole Products, Female Plug, 150 Amp Series, Green

Application

- Temporary Electrical Power

Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

General

Catalog Number	HBL15FGN
Color	Green
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Female Plug
Material	Brass and Non-Metallic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none">• Base Compound - Thermoplastic Elastomer (TPE)• Contact Material - Brass• Retaining Screw Material - Nylon
Style	Female
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	783585458410

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	150 A
Connectivity	Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Voltage Rating Description	600V AC/DC

Conductor Related

Conductor Range	#8 AWG to #2 AWG SC/PPC Wire
Number of Conductors	1 Conductor

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
Pallet Quantity	4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Single Pole Devices](#)
[Specifications - HBL15FGN](#)
[Warranty - Industrial & Commercial Products](#)