

## Single Pole Products, Female Plug, 150 Amp Series, Red

By Hubbell Wiring Device-Kellems  
Catalog # [HBL15FR](#)



Single Pole Products, Female Plug, 150 Amp Series, Red

### General

Application	Temporary Electrical Power
Catalog Number	HBL15FR
Color	Red
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Female Plug
Material	Brass and Non-Metallic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	1-Pole
Performance	Electrical - Amperage Rating - 150A Maximum Electrical - Voltage Ratings - 600V AC Maximum 250V DC Maximum Mechanical - Product Identification - Ratings are a permanent part of device Mechanical - Terminal Accommodation - #8 to #2 AWG
Series	Series 15
Style	Female
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	783585458397

### Dimensions

Display Size	Standard
--------------	----------

### Electrical Ratings

Amperage Rating	150 A
Connectivity	Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Voltage Rating Description	600V AC/DC

### Conductor Related

Conductor Range	#8 AWG to #2 AWG SC/PPC Wire
Number of Conductors	1 Conductor

### Certifications And Compliance

Industry Standard(s)	National Electric Code (NEC), ANSI/NFPA 70 UL and cUL Listed UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

### Logistics

Carton Quantity	25
Pallet Quantity	4500

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Single Pole Devices](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL15FR-SPEC-EN | REV 6/2024