

Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL15FRBK](#)



Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, Black

Features

- Double Set Screw Termination
- 150 Amp Series
- Black

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

General

Catalog Number	HBL15FRBK
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Female Receptacle
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none">• Base Compound - Thermoplastic Elastomer (TPE)• Contact Material - Brass• Mounting Hole - 3x Ø .20"• Retaining Screw Material - Nylon• Termination - (2) 5/32 Socket Head Set Screws
Style	Double Set Screw Female

Type	Receptacle
UPC	783585458175

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	150 A
Connectivity	Double Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	90000

Conductor Related

Number Of Wires	None
Wire Size	#4 AWG Type SC/PPC Wire

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
Pallet Quantity	4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Single Pole Devices](#)
[Specifications - HBL15FRBK](#)
[Warranty - Industrial & Commercial Products](#)