

## Straight Blade Devices, Female Connector Body, Elasto-Grip Water Tight, Industrial/Commercial Grade, Straight, 125V, 15A 5-15R

By Hubbell Wiring Device-Kellems  
Catalog # [HBL15W47](#)

Straight Blade Devices, Female Connector Body, Elasto-Grip Water Tight, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 125V, 15A 5-15R, Yellow, Single Pack.



### Application

- Industrial/Commercial

### Performance

- Electrical: Current Interrupting: Certified for current interrupting at full rated current
- Dielectric Voltage: Withstands 2,000V minimum
- Mechanical: Product Identification: Terminal Accommodation: #18-#12 AWG. Stranded copper wire only. Terminal Identification: Terminals identified in accordance with UL 498 and CSA
- Environmental: Flammability UL 94 HB or better
- IP Suitability: IP55
- Operating Temperatures: Maximum continuous 75°C
- minimum -40°C (w/o impact)

### General

Catalog Number	HBL15W47
Cord Range	0.250"-0.655" (6.4-16.6)
EU RoHS Indicator	No
Environmental Conditions	Watertight
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Elastogrip
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Elastogrip
Specifications	<ul style="list-style-type: none"> <li>Assembly Screws - Plated steel</li> <li>Contact Holder - Nylon</li> <li>Contacts - .040" (1.0) Brass</li> <li>Housing - Thermoplastic Elastomer</li> <li>Terminal Clamp - Nickel plated steel</li> <li>Terminal Retainer - Clear Polycarbonate</li> </ul>

Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Connector Body
UPC	783585013022

### Dimensions

Dimensions	4.03 in x 1.76 in x 4.03 in
Display Size	Standard
Height	4.03 in
Length	4.03 in
Weight	0.35 lb
Width	1.76 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

### Conductor Related

Conductor Range	#18 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>CSA Certified to C22.2 No. 42 File 280C</li> <li>NEMA® WD-6 Compliant</li> <li>UL Listed to UL498 File E1706</li> </ul>
Nema Rating	5-15R

Standards - RoHS Compliance CM  
Status

### Logistics

Carton Quantity 10  
Pallet Quantity 1200

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL15W47](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL15W47-SPEC-EN | REV 10/2024