

Temporary Lighting Products, 20' 18/2 STW Single 6.6W 90 LED Fixture, 450 Lumen Output Per Fixture

By Hubbell Wiring Device-Kellems
Catalog # [HBL182S20LED](#)



Temporary Lighting Products, 20' 18/2 STW Single 6.6W 90 LED
Fixture, 450 Lumen Output Per Fixture

Performance

- Electrical - Lamp Life - 50,000 hours
- Electrical - Lumen Output per Fixture - 450
- Electrical - Rating - 15A 125V
- Electrical - Watt per fixture - 6.6
- Mechanical - Cord Length - 20 ft.
- Mechanical - Number of fixtures - 1

General

Catalog Number	HBL182S20LED
EU RoHS Indicator	Contact Manufacturer
Series	Stringer Lights
Specifications	<ul style="list-style-type: none">• Included - Magnetic base• Light Type - LED• Plug Type - NEMA 5-15P
Type	LED Stringer Lights
UPC	783585528311

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA• ETL• UL
----------------------	--

Logistics

Carton Quantity	1
Pallet Quantity	192

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL182S20LED](#)
[Warranty - Industrial & Commercial Products](#)