

# Locking Devices, Hubbellock, Industrial, Male Plug, 30A 3-Phase 480V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Red

By Hubbell Wiring Device-Kellems  
Catalog # [HBL20445B](#)



Locking Devices, Hubbellock®, Industrial, Male Plug, 30A 3-Phase 480V AC, 3-Pole 4-Wire Grounding Hubbellock® Plug, Red nylon housing, Thermoset interior, Non-NEMA, Screw Terminal

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage Withstand - 2,000V minimum
- Environmental - Flammability - UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL20445B
Color	Black, White
Cord Range	0.700"-1.200" (17.78-30.5)
EU RoHS Indicator	Contact Manufacturer
Item Type	30A Hubbellock® Plug
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Stainless Steel</li><li>• Contacts - Brass</li><li>• Cord Clamp Material - PET</li><li>• Device Color - Black/White</li><li>• Housing - Nylon</li><li>• Plug Housing - Thermoset</li><li>• Terminal Screws - Zinc plated steel</li></ul>
Type	Plugs
UPC	783585017266

## Dimensions

Dimensions	2.33 in x 0.94 in x 5.63 in
Height	5.63 in
Length	2.33 in
Weight	0.9 lb
Width	0.94 in

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

## Conductor Related

Cable Range	0.700 - 1.200 in
Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA Standard</li><li>• Listed to UL Standard</li></ul>
----------------------	---

## Logistics

Carton Quantity	1
Pallet Quantity	980

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL20445B](#)  
[Warranty - Industrial & Commercial Products](#)