

# Metal PlugTrak, Isolated Ground, 15A 1 Circuit, 5 Receptacle, 5' Length, Gray



By Hubbell Wiring Device-Kellems  
Catalog # [HBL20IG512GY](#)

Metal PlugTrak, Isolated Ground, 15A 1 Circuit , 5 Receptacle, 5'  
Length, Gray

## Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

## General

Catalog Number	HBL20IG512GY
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	5
Series	Metal
Specifications	<ul style="list-style-type: none"><li>• Number of Receptacles - 5 Singles</li><li>• PlugTrak Amperage - 15A</li><li>• PlugTrak Length - 5 Foot</li><li>• Receptacle Face - Thermoplastic</li><li>• Spacing - 12 Inch OC</li><li>• Wiring Type - Hard Wired</li></ul>
Style	Isolated Ground
Type	Single Circuit
UPC	783585214801

## Dimensions

Length 5 ft

## Electrical Ratings

Current / Amperage Rating 15 A

## Conductor Related

Wire Size #12 AWG THHN

## Certifications And Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E253976 /E253830 /E253833
- UL Standard UL 5

## Logistics

Carton Quantity 2  
Pallet Quantity 540

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL20IG512GY](#)  
[Warranty - Industrial & Commercial Products](#)