

Locking Devices, Hubbellock, Industrial, Male Plug, 30A 600V AC, 20A 250V DC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL21415B](#)



Locking Devices, Hubbellock®, Industrial, Male Plug, 30A 600V AC, 20A 250V DC, 3-Pole 4-Wire Grounding Hubbellock® Plug, Black nylon housing, thermoplastic interior, Non-NEMA, Screw Terminal, Black and White

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage Withstand - 2,000V minimum
- Environmental - Flammability - UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL21415B
Color	Noir, blanc
Cord Range	0.700"-1.200" (17.78-30.5)
EU RoHS Indicator	Contact Manufacturer
Item Type	20A/30A Hubbellock® Plug
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Stainless Steel• Contacts - Brass• Cord Clamp Material - PET• Device Color - Black/White• Housing - Nylon• Plug Housing - Thermoset• Terminal Screws - Zinc plated steel
Type	Plugs

UPC 783585017273

Dimensions

Dimensions	2.33 in x 0.94 in x 5.63 in
Height	5.63 in
Length	2.33 in
Weight	0.8 lb
Width	0.94 in

Electrical Ratings

Amperage Rating	20/30 A
Current / Amperage Rating	20/30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Cable Range	0.700 - 1.200 in
Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA Standard• Listed to UL Standard
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	910

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL21415B](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand