

# Locking Devices, Hubbellock, Industrial, Flanged Receptacle, 30A 600V AC, 20A 250V DC, 3-Pole 4- Wire Grounding, Non- NEMA



By Hubbell Wiring Device-Kellems  
Catalog # [HBL21420](#)

Locking Devices, Hubbellock®, Industrial, Flanged Receptacle, 30A 600V AC, 20A 250V DC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum angle housing, with 3/4" N P T hub for surface mounting, Metallic

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - UL 94 V0 for Receptacles and Inlets.HB or better for Plugs and Connectors
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #10 AWG - #6 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL21420
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A/30A Grounding Hubbellock® Receptacle
Material	Aluminum, Cast
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Contacts - Bronze</li><li>• Housing - Cast Aluminum</li><li>• Receptacle Interior - Thermoset</li><li>• Terminal Screws - Zinc plated steel</li></ul>
Type	Receptacle

UPC 783585017426

## Dimensions

Dimensions	5.93 in x 3.06 in x 5.09 in
Display Size	Standard Sized Product
Height	5.09 in
Length	5.93 in
Weight	2 lb
Width	3.06 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

## Logistics

Carton Quantity	10
Pallet Quantity	360

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL21420](#)  
[Warranty - Industrial & Commercial Products](#)