

## Locking Devices, Twist-Lock®, Safety Shroud, Male Plug, 20A 125V, 2-Pole 3-Wire Grounding, L5-20P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2311S](#)



Locking Devices, Twist-Lock®, Safety-Shroud®, Male Plug, 20A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-20P, Screw Terminal, Black and White Nylon Body, White PBT Shroud.

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL2311S
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	20A Safety-Shroud® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> <li>• Assembly Screws - Steel - nickel plated</li> <li>• Blades - Brass</li> <li>• Housing / Cord Clamp - Nylon</li> <li>• Safety-Shroud® - White PBT</li> <li>• Terminal Clamp - Cold rolled steel - nickel plated</li> <li>• Terminal Retainer - Clear polycarbonate</li> <li>• Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)</li> </ul>

Type	Plugs
UPC	783585234069

### Dimensions

Dimensions	2.26 in x 2.04 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.26 in
Weight	0.35 lb
Width	2.04 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Cable Range	0.360 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	L5-20P
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
-----------------	----

Pallet Quantity

2160

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL2311S](#)

[Warranty - Industrial & Commercial Products](#)

**Product Assets**



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2311S-SPEC-EN | REV 10/2024