

Locking Devices, Twist-Lock®, Insulgrip® Plug, 20A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-20P, Black nylon

By Hubbell Wiring Device-Kellems
Catalog # [HBL2321BK](#)



Locking Devices, Twist-Lock®, Insulgrip® Plug, 20A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-20P, Black nylon

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2321BK
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	20A Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Steel - nickel plated• Blades - Brass• Housing / Cord Clamp - Nylon• Terminal Clamp - Cold rolled steel - nickel plated• Terminal Retainer - Clear polycarbonate

UPC

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- 783585172224

Dimensions

Dimensions	2.26 in x 2.26 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.26 in
Weight	0.4 lb
Width	2.26 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L6-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
-----------------	---

Pallet Quantity

2880

Catalogs - WDK Catalog Full 2024

Specifications - HBL2321BK

Warranty - Industrial & Commercial Products

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2321BK-SPEC-EN | REV 10/2024