

Locking Devices, Twist-Lock®, Industrial, Shrouded, Male Plug, 20A 250V, 2-Pole 3-Wire Grounding, L6-20P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2321S](#)



Locking Devices, Twist-Lock®, Industrial, Safety-Shroud®, Male Plug, 20A 250V, 2-Pole 3-Wire Grounding, NEMA L6-20P, Screw Terminal, Black and White nylon body, White PBT Shroud.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2321S
Color	Black, White
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	20A Male Safety-Shroud® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Steel - nickel plated• Blades - Brass• Housing / Cord Clamp - Nylon• Safety-Shroud® - White PBT• Terminal Clamp - Cold rolled steel - nickel plated• Terminal Retainer - Clear polycarbonate

Type
UPC

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Plugs
783585234144

Dimensions

Dimensions	2.26 in x 2.26 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.26 in
Weight	0.25 lb
Width	2.26 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Cable Range	0.325 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L6-20P

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10
Pallet Quantity 2160

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2321S](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2321S-SPEC-EN | REV 10/2024