

Locking Devices, Twist-Lock®, Safety Shroud, Surface Mount Receptacle, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL2410SR](#)



Locking Devices, Twist-Lock®, Safety-Shroud®, Surface Mount Receptacle, One Gang, 20A 125/250V AC, 3-Pole 4-Wire Grounding, NEMA L14-20R, Screw Terminal, Gray

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2410SR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2(1)
Item Type	20A Safety-Shroud® Receptacle
Material	Valox™
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Body Contact Carrier - Natural (white) nylon• Body Holding Screws - Steel, zinc plated• Contacts - Brass• Housing / Flange - Gray RPT• Terminal Retainer - Clear polycarbonate
Type	Surface Mount Receptacle
UPC	783585234427

Dimensions

Dimensions	4.56 in x 2.84 in x 1.71 in
Display Size	Standard Sized Product
Height	1.71 in
Length	4.56 in
Weight	0.45 lb
Width	2.84 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L14-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand