



Locking Devices, Twist-Lock®, Watertight Safety Shroud, Receptacle, 20A 125/250V, 3-Pole 4-Wire Grounding, L14- 20R, Screw Terminal, Gray



By Hubbell Wiring Device-Kellems
Catalog # [HBL2410SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®,
Receptacle, 20A 125/250V AC, 3-Pole 4-Wire Grounding,
NEMA L14- 20R, Screw Terminal, PBT housing and flange,
Gray.

Features

- High impact, thermoplastic housing for heavy-duty industrial environments
- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use

Application

Heavy Duty Industrial Shrouded Watertight

General

Environmental Conditions	Watertight
Horsepower - Maximum	2 (1)
Item Type	Receptacles
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16

Dimensions

Dimensions	3.75 in x 3.75 in x 2.90 in
Display Size	Standard Sized Product
Height	2.90 in
Length	3.75 in
Weight	0.55 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L14-20R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

AWG - #8 AWG solid or
stranded copper wire only.

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498

Type
UPC

Receptacle
783585231266



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL2410SW-SPEC-EN | REV 1/2024