

Locking Devices, Twist-Lock®, Watertight Safety Shroud, Receptacle 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15- 20R, Screw Terminal, Gray



By Hubbell Wiring Device-Kellems
Catalog # [HBL2420SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®,
Receptacle 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire
Grounding, NEMA L15-20R, Screw Terminal, PBT housing and
flange, Gray.

Application

Heavy Duty Industrial Shrouded Watertight

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2420SW
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Horsepower - Maximum	3
Item Type	Receptacles
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Body Contact Carrier - Natural (white) nylon • Contacts - Brass • Drive Screws - Steel, zinc plated • Housing / Cover - Gray RPT • Lift-Cover Spring & Pin - Stainless Steel

Type
UPC

- Terminal Retainer - Clear polycarbonate
- Receptacle
783585231341

Dimensions

Dimensions	3.75 in x 3.75 in x 2.90 in
Display Size	Standard Sized Product
Height	2.9 in
Length	3.75 in
Weight	0.6 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	250 V
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L15-20R

Logistics

Carton Quantity	5
Pallet Quantity	1000



A Hubbell brand