

Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 20A 3 Phase WYE 120/208V AC, 4-Pole 4-Wire Non- Grounding, L18-20R, Screw Terminal, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL2440](#)



Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 20A 3 Phase WYE 120/208V AC, 4-Pole 4-Wire Non- Grounding, NEMA L18-20R, Screw Terminal, Nylon face, back and side wire, Black

Application

Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2440
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Single Flush Receptacles
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - Glass-Reinforced thermoplastic polyester (RTP)• Contacts - Brass• Face - Nylon• Mounting Strap - Brass• Terminal Screws - #10 - 32 Brass

Type
UPC

Single Flush Receptacle
783585235790

Dimensions

Dimensions
Display Size
Height
Length
Weight
Width

3.28 in x 1.7 in x 1.23 in
Standard Sized Product
1.23 in
3.28 in
0.3 lb
1.7 in

Electrical Ratings

Amperage Rating
Connectivity
Current / Amperage Rating
Current Rating
Dielectric Strength
Phase
Voltage Rating
Voltage Rating Description

20 A
Back and Side Wired Screw Terminals
20 A
20 A
Withstands 2,000V minimum
3 Phase WYE
3 Phase WYE 120/208 VAC
3 Phase WYE 120/208 VAC

Conductor Related

Number Of Wires
Wire Size

4-Wire
#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)

- Certified to CSA C22.2 No.42
- Fed.Spec. W-C-596
- Listed to UL 498

Nema Rating
Standards - RoHS Compliance
Status

L18-20R
CM

Logistics

Carton Quantity 10
Pallet Quantity 2520

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2440](#)
[Warranty - Industrial & Commercial Products](#)

Product Assets



©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2440-SPEC-EN | REV 10/2024