

## Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 3-Phase 347/600V AC, 4-Pole 4-Wire Non-Grounding, L20-20P, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems  
Catalog # [HBL2461](#)

Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 3-Phase Y 347/600V AC, 4-Pole 4-Wire Non-Grounding, NEMA L20-20P, Screw Terminal, Black and White Nylon

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL2461
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Male Non-Grounding Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> <li>• Assembly Screws - Steel - nickel plated</li> <li>• Blades - Brass</li> <li>• Housing / Cord Clamp - Nylon</li> <li>• Terminal Clamp - Cold rolled steel - nickel plated</li> <li>• Terminal Retainer - Clear polycarbonate</li> <li>• Terminal Screws - #10-32 Brass (Phillips / Slotted /</li> </ul>

Type	Robertson)
UPC	Plugs 783585038438

### Dimensions

Dimensions	2.33 in x 2.33 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.33 in
Weight	0.3 lb
Width	2.33 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	3 Phase WYE 347/600 VAC
Voltage Rating Description	3 Phase WYE 347/600 VAC

### Conductor Related

Cable Range	0.350 - 1.150 in
Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	L20-20P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity 30

Catalogs - WDK Catalog Full 2024  
Specifications - HBL2461  
Warranty - Industrial & Commercial Products

## Product Assets

---



©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2461-SPEC-EN | REV 10/2024